





Product Category

※ Please click on series names for related specifications.

Photo	Series	Cooling method	Built-in active PFC	
	High cost-performance/Conformal coated NEL series 400W (2.8V/4.2V/5V)	Built-in cooling fan	No	
	Slim and Low Profile /Conduction Power/Semi-potted LSP series 160W (3.3V/4.2V/5V)	Conduction cooling		Yes
	Conduction Power/Semi-potted UHP series 200W~500W (3.3V/4.2V/4.5V/5V)	Conduction cooling		Yes
	Conduction Power/Conformal coated HSP series 200W~300W (2.8V/4.2V/5V)	Conduction cooling		Yes

LED Display Power

With Fan/
Non PFC

High cost-performance

NEL-400 Series



Slim and Low Profile /Conduction Power/Semi-potted

LSP-160 Series



Low Profile /Conduction Power/Semi-potted

UHP-200A/200/350/500 Series



Low Profile /Conduction Power/Power/Conformal coated

HSP-200/300 Series



100 150 200 250 300 350 400 450 500 550 600 700 800 瓦数