

SUSTAINABLE
DEVELOPMENT
GROUP



LRS-450/600 Series

450W & 600W Enclosed Type PSU

MEAN WELL

Product introduction

- MW **Patent** circuitry& case design (202220241473.0,202230060511.8)
- 1U design (Pitch **refer to SE & LRS**)
- **90~264Vac** (select by switch)
- High efficiency up to **92%**
- OLP: **CCL** 3s shut down
- **MTBF > 1kk**
- 3 years warranty



LRS-450



LRS-600



R33100
RoHS

IS 13252(Part 1):2010/
IEC 60950-1:2005
8
R-41179035



AS/NZS62368-1



TP TC004



IEC62368-1



UL62368-1



(Note.9)






LRS Vs SE Comparison

	NEW	
	LRS-450	SE-450
Price	\$	\$\$
Model(V)	5/12/15/24/36/48	3.3/5/12/15/24/36/48
Dimension(mm)	225*124*35	225*124*50
Effi.(Typ.)	92%	88%
AC input range	90~132/180~ 264Vac (select by switch)	
Operation temp.	5V: 45°C Other V: 50°C	3.3/5/12V: 45°C Other V: 50°C
OLP	C.C limiting, shut down after 3s	Shut down
Photo		

	NEW	
	LRS-600	SE-600
Price	\$	\$\$
Model(V)	5/12/15/24/27/36/48	
Dimension(mm)	225*124*41	247*127*63.5
Effi.(Typ.)	92%	88%
AC input range	90~132/180~ 264Vac (select by switch)	
Operation temp.	5V: 45°C Other V: 50°C	All V: 40°C
OLP	C.C limiting, shut down after 3s	Shut down
Photo		

LRS Vs SE Application

機型名稱	產品照	應用
SE-450/600 Series	 OLP: Hiccup mode	 
LRS-450/600 Series	 OLP: C.C limiting, shut down after 3s	 



SUSTAINABLE
DEVELOPMENT
GROUP



Your Reliable Power Partner