


# Product Category

## Charger

※ Please click on series names for related introduction webpages or specifications.

Category	Type	Photo	Series	Warranty	Remark
Portable	Desktop type		<a href="#"><u>ENP/ENC series</u></a> 120/ 180/ 240/ 360W	3 years	Programmable
	Adaptor type		<a href="#"><u>GC series</u></a> 30/ 120/ 160/ 220/ 330W	2 years	
			<a href="#"><u>NPB series</u></a> 120/ 240/ 360W	3 years	2/3 stage and Vo/Io Adj. ( NPB-120~360 )
Stationary	Screw Mounted		<a href="#"><u>NPB/NPP series</u></a> 450/ 750/ 1200/ 1700W	3 years	NPB : Intelligent / CANBus <b>NEW</b> Setting parameter of charger via wireless NFC NPP : 2-in-1 ( PSU + Charger)
			<a href="#"><u>HEP-600C series</u></a> <a href="#"><u>HEP-1000 series</u></a> 600W 1000W	6 years	1. Programmable 2. Harsh Environment
			<a href="#"><u>RPB-1600 series</u></a> <a href="#"><u>DBU-3200 series</u></a> 1600W 3200W	5 years	Programmable
	Rack-Mounted		<a href="#"><u>RCB-1600 series</u></a> <a href="#"><u>DBR-3200 series</u></a> 1600W 3200W	5 years	1. Rack type , hot-swop 2. Programmable

# Road Map Charger



# Road Map Charger

Stationary

Screw mounted

Rack-mounted

Internal potted for harsh environment  
**HEP-600C/ 1000C Series**



※ Red words is new product

Vo/Io Programmable  
**RPB-1600/ DBU-3200 Series**



NPB : Intelligent charger  
 NPP : Charger or power supply mode selectable (2-in-1)  
**NPB-450/ 750/ 1200/ 1700 Series**  
**NPP-450/ 750/ 1200/ 1700 Series**



( NPB-450~1700 )  
 DC output side(Non-NFC Model)



**NEW**  
 ( NPB-450-NFC only )  
 DC output side (NFC Model)



Vo/Io Programmable  
**RCB-1600 / DBR-3200 Series**



360      720      1000      1600      3200      →      Watt

# Product Category

## Inverter

※ Please click on series names for related introduction webpages or specifications.

Category	Photo	Series	Warranty
True sine wave		<u>TN series</u> DC-AC + Charger + AC_by pass(UPS) 1500/ 3000W	3 years
		<u>NTS series</u> DC-AC 250/ 300/ 400/ 450/ 750/ 1200/ 1700/ 2200/ 3200W	
		<u>NTU series</u> DC-AC + AC_by pass (UPS) 1200/ 1700/ 2200/ 3200W	5 years
Square sine wave		<u>A301/A302 series</u> DC-AC 100/ 150/ 300/ 600/ 1000/ 1700/ 2500W	1 year


# Road Map Inverter

※ Red words is new product

True Sine Wave



Square Sine Wave



DC-AC + AC & Solar charger + AC bypass  
**TN-1500 / 3000 Series**



DC-AC  
**NTS-250P/ 400P, NTS-300 / 450 / 750 / 1200 / 1700 / 2200 / 3200 Series**

DC-AC + AC bypass UPS function  
**NTU-1200 / 1700 / 2200 / 3200 Series**



**NEW**

DC-AC + AC Charger + AC bypass + AC Output Parallel  
**NTN-5K Series**



DC-AC+ Solar MPPT charger  
**ISI-501**



Remote controller  
**IRC-1/2/3**



DC-AC  
**A301/2-100 / 150 / 300 / 600 / 1000 / 1700 / 2500 Series**



100 200 300 500 700 1000 1500 3000 5000 Watt