


※ Red words are new products
 ※ Please click on series names for related introduction webpages or specifications.

Category	Type	Photo	Series	Warranty	Remark
Portable	Desktop type		<u>ENP/ENC series</u> 120/ 180/ 240/ 360W	3 years	Programmable
	Adaptor type		<u>GC series</u> 30/ 120/ 160/ 220/ 330W	2 years	
			<u>NPB series</u> 120/ 240/ 360W	3 years	2/3 stage and Vo/Io Adj. (NPB-120~360)
Stationary	Screw Mounted		<u>NPB/NPP series</u> 450/ 750/ 1200/ 1700W	3 years	NPB : Intelligent / CANBus NPP : 2-in-1 (PSU + Charger)
			<u>HEP-600C series</u> <u>HEP-1000 series</u> 600W 1000W	6 years	1. Programmable 2. Harsh Environment
			<u>RPB-1600 series</u> <u>DBU-3200 series</u> 1600W 3200W	5 years	Programmable
	Rack-Mounted		<u>RCB-1600 series</u> <u>DBR-3200 series</u> 1600W 3200W	5 years	1. Rack type , hot-swop 2. Programmable

Road Map Charger



Road Map Charger

Stationary

Screw mounted

Rack-mounted

Internal potted for harsh environment
HEP-600C/ 1000C Series



Vo/Io Programmable
RPB-1600/ DBU-3200 Series



NPB : Intelligent charger
NPP : Charger or power supply mode selectable (2-in-1)
NPB-450/ 750/ 1200/ 1700 Series
NPP-450/ 750/ 1200/ 1700 Series



Vo/Io Programmable
RCB-1600 / DBR-3200 Series






360 720 1000 1600 3200 Watt

Product Category

Inverter

※ Red words are new or under development products
 ※ Please click on series names for related introduction webpages or specifications.

Category	Photo	Series	Warranty
True sine wave		<u>TN series</u> DC-AC + Charger + AC_by pass(UPS) 1500/ 3000W	3 years
	 NEW	<u>NTS series</u> DC-AC 250/ 300/ 400/ 450/ 750/ 1200/ 1700/ 2200/ 3200W	
		<u>NTU series</u> DC-AC + AC_by pass (UPS) 1200/ 1700/ 2200/ 3200W	
Square sine wave		<u>A301/A302 series</u> DC-AC 100/ 150/ 300/ 600/ 1000/ 1700/ 2500W	1 year

Road Map Inverter

※ Red words are new or under development products

True Sine Wave



Square Sine Wave

