

Model	ES Class (output circuit)	PS Class (output circuit)	Meet LPS	SELV
AD-55	ES1	PS2	N	Y
ADD-55	ES1	PS2	N	Y
ADS-55	ES1	PS2	N	Y
AD-155	ES1	PS3	N	Y
ADD-155	ES1	PS3	N	Y
ADS-155	ES1	PS3	N	Y
AD-155C	ES2	PS3	N	Y
ADD-155C	ES2	PS3	N	Y
CSP-3000	ES3	PS3	N	N
DBR-3200	ES1	PS3	N	Y
DBU-3200	ES1	PS3	N	Y
DPU-3200	ES1	PS3	N	Y
NSP-3200	ES1	PS3	N	Y
DHB-12K1UT	ES1	PS3	N	Y
DHP-12K1UT	ES1	PS3	N	Y
DHP-1UT-A	ES1	PS3	N	Y
DBUF20-24	ES1	PS3	N	Y
DBUF40-24	ES1	PS3	N	Y
DDR-15	ES1	PS2	N	Y
DDR-30	ES1	PS2	N	Y
DDR-60	ES1	PS2	N	Y
DDR-120	ES1	PS3	N	Y
DDR-240	ES1	PS3	N	Y
DDR-480	ES1	PS3	N	Y
DETN01	ES1	PS1	N	Y
SBTN01	ES1	PS1	N	Y
SFTN01	ES1	PS1	N	Y
DRA-40	ES1	PS2	Y	Y
DRA-60	ES1	PS2	Y	Y
DRC-40	ES1	PS2	Y	Y
DRC-60	ES1	PS2	Y	Y
DRC-100	ES1	PS2	N	Y
DRC-180	ES1	PS3	N	Y
DRDN20	ES1	PS3	N	Y
DRDN40	ES1	PS3	N	Y
ERDN20	ES1	PS3	N	Y
ERDN40	ES1	PS3	N	Y
DRS-240	ES1	PS3	N	Y
DRS-480	ES1	PS3	N	Y
EDR-75	ES1	PS2	N	Y
NDR-75	ES1	PS2	N	Y
EDR-150-24	ES1	PS3	N	Y
EDR-120	ES1	PS3	N	Y
NDR-120	ES1	PS3	N	Y
ELP-75	ES1	PS2	N	Y
ENC-120	ES1	PS3	N	Y
ENP-120	ES1	PS3	N	Y
ENC-180	ES1	PS3	N	Y
ENC-240	ES1	PS3	N	Y
ENP-180	ES1	PS3	N	Y
ENP-240	ES1	PS3	N	Y
ENC-360	ES1	PS3	N	Y
ENP-360	ES1	PS3	N	Y
EPP-100	ES1	PS3	N	Y
EPP-150	ES1	PS3	N	Y
EPP-120S	ES1	PS3	N	Y
EPP-200	ES1	PS3	N	Y

Model	ES Class (output circuit)	PS Class (output circuit)	Meet LPS	SELV
EPP-300	ES1	PS3	N	Y
EPP-400	ES1	PS3	N	Y
EPP-500	ES1	PS3	N	Y
EPS-15	ES1	PS2	N	Y
EPS-25	ES1	PS2	Y	Y
EPS-35	ES1	PS2	Y	Y
EPS-45	ES1	PS3	N	Y
EPS-65	ES1	PS3	N	Y
EPS-45S	ES1	PS2	Y	Y
EPS-65S	ES1	PS2	Y	Y
EPS-120	ES1	PS3	N	Y
ERP-200	ES1	PS3	N	Y
ERP-350	ES1	PS3	N	Y
ERPF-400	ES1	PS3	N	Y
GC30(U,B,E)	ES1	PS2	Y	Y
GC120A	ES1	PS3	N	Y
GC160A	ES1	PS3	N	Y
GC220A	ES1	PS3	N	Y
GC330A	ES1	PS3	N	Y
GST280A	ES1	PS3	N	Y
GS120A	ES1	PS3	N	Y
GST120A	ES1	PS3	N	Y
GST18B,E,U	ES1	PS2	Y	Y
GST25B,E,U	ES1	PS2	Y	Y
GST36B,E,U	ES1	PS2	Y	Y
GST18A	ES1	PS2	Y	Y
GST25A	ES1	PS2	Y	Y
GST40A	ES1	PS2	Y	Y
GST60A	ES1	PS2	Y	Y
GST90A	ES1	PS3	N	Y
GST120A	ES1	PS3	N	Y
GA120A	ES1	PS3	N	Y
GST160A	ES1	PS3	N	Y
GST220A	ES1	PS3	N	Y
GST360A	ES1	PS3	N	Y
GST360B	ES1	PS3	N	Y
HDP-190	ES1	PS3	N	Y
HDP-240	ES1	PS3	N	Y
HDR-15	ES1	PS2	Y	Y
HDR-30	ES1	PS2	Y	Y
HDR-60	ES1	PS2	Y	Y
HDR-100	ES1	PS2	Y	Y
HDR-100-xN	ES1	PS3	N	Y
HDR-150	ES1	PS3	N	Y
HEP-240	ES1	PS3	N	Y
HLG-240	ES1	PS3	N	Y
HEP-100	ES1	PS3	N	Y
HEP-150	ES1	PS3	N	Y
HEP-185	ES1	PS3	N	Y
HEP-320	ES1	PS3	N	Y
HEP-480	ES1	PS3	N	Y
HEP-600(C)	ES1	PS3	N	Y
HEP-1000	ES1	PS3	N	Y
HEP-1000-100y	ES2	PS3	N	N
HEP-2300-55Wz	ES1	PS3	N	Y
HEP-2300-115Wz, HEP-2300-230Wz, HEP-2300-380Wz	ES3	PS3	N	N
HRP-150	ES1	PS3	N	Y

Model	ES Class (output circuit)	PS Class (output circuit)	Meet LPS	SELV
HRPG-150	ES1	PS3	N	Y
HRP-200	ES1	PS3	N	Y
HRPG-200	ES1	PS3	N	Y
HRP-300	ES1	PS3	N	Y
HRPG-300	ES1	PS3	N	Y
HRP-450	ES1	PS3	N	Y
HRPG-450	ES1	PS3	N	Y
HRP-600	ES1	PS3	N	Y
HRPG-600	ES1	PS3	N	Y
HRP-75	ES1	PS2	N	Y
HRP-100	ES1	PS3	N	Y
HRP-150N,N3	ES1	PS3	N	Y
HRP-300N	ES1	PS3	N	Y
HRP-600N	ES1	PS3	N	Y
HRPG-1000	ES1	PS3	N	Y
PSPA-1000	ES1	PS3	N	Y
HSP-200	ES1	PS3	N	Y
HSP-300	ES1	PS3	N	Y
IRM-01	ES1	PS1	Y	Y
IRM-02	ES1	PS1	Y	Y
IRM-03	ES1	PS1	Y	Y
IRM-05	ES1	PS2	Y	Y
IRM-10	ES1	PS2	Y	Y
IRM-15	ES1	PS2	Y	Y
IRM-20	ES1	PS2	Y	Y
IRM-30,30ST	ES1	PS2	Y	Y
IRM-45(ST)	ES1	PS2	Y	Y
IRM-60(ST)	ES1	PS2	Y	Y
IRM-90(ST)	ES1	PS3	N	Y
ISI-501	ES1	PS3	N	Y
LAD-240	ES1	PS3	N	Y
LAD-360	ES1	PS3	N	Y
LAD-360U	ES1	PS3	N	Y
LPC-20	ES1	PS2	Y	Y
LPV-20	ES1	PS2	Y	Y
LPC-60	ES1	PS2	Y	Y
LPV-60	ES1	PS2	Y	Y
LPC-100	ES3	PS3	N	N
LPC-150	ES3	PS3	N	N
LPH-18	ES1	PS2	Y	Y
LPP-100	ES1	PS3	N	Y
LPP-150	ES1	PS3	N	Y
LPS-50 except LPS-50-48	ES1	PS2	N	Y
LPS-50-48	ES2	PS2	N	Y
LPS-75 except LPS-75-24	ES1	PS2	N	Y
LPS-75-24	ES1	PS2	Y	Y
LPS-100	ES1	PS3	N	Y
LPV-35	ES1	PS2	Y	Y
LPC-35	ES1	PS2	Y	Y
LPV-100	ES1	PS3	N	Y
LPV-150	ES1	PS3	N	Y
LRS-35-5, LRS-50-3.3 and LRS-50-5	ES1	PS3	N	Y
LRS-35,50 except LRS-35-5, LRS-50-3.3 and LRS-50-5	ES1	PS2	Y	Y
LRS-75-12	ES1	PS3	N	Y
LRS-75 except LRS-75-12	ES1	PS2	Y	Y
LRS-100	ES1	PS3	N	Y
LRS-150,150F	ES1	PS3	N	Y

Model	ES Class (output circuit)	PS Class (output circuit)	Meet LPS	SELV
LRS-200	ES1	PS3	N	Y
LRS-350	ES1	PS3	N	Y
LRS-450	ES1	PS3	N	Y
LRS-600	ES1	PS3	N	Y
LSP-160	ES1	PS3	N	Y
MDR-10	ES1	PS2	N	Y
MDR-20	ES1	PS2	N	Y
MDR-40	ES1	PS2	N	Y
MDR-60	ES1	PS2	N	Y
MDR-100	ES1	PS3	N	Y
MP1K0	ES1	PS3	N	Y
MP450	ES1	PS3	N	Y
MP650	ES1	PS3	N	Y
NDR-240	ES1	PS3	N	Y
NDR-480	ES1	PS3	N	Y
NMP1K2,NMS,NMD-240	ES1	PS3	N	Y
NMP650,NMS,NMD-240	ES1	PS3	N	Y
NPB-750-12, NPB-750-24	ES1	PS3	N	Y
NPB-750-48	ES2	PS3	N	N
NPP-750-12, NPP-750-24	ES1	PS3	N	Y
NPP-750-48	ES2	PS3	N	N
NPP-1200-x (where x can be 12, 24)	ES1	PS3	N	Y
NPP-1200-48	ES2	PS3	N	N
NPB-1200-x (where x can be 12, 24)	ES1	PS3	N	Y
NPB-1200-48	ES2	PS3	N	N
NPB-1700-12, NPP-1700-12, NPB-1700-24, NPP-1700-24	ES1	PS3	N	Y
NPB-1700-48	ES2	PS3	N	N
NPP-1700-48	ES2	PS3	N	N
NPB-120-12TB, NPB-120-12AD1-A, NPB-120-12XLR-A, NPB-120-24TB, NPB-120-24AD1-A, NPB-120-24XLR-A, NPB-240-12TB, NPB-240-12AD1, NPB-240-12XLR, NPB- 240-24TB, NPB-240-24AD1, NPB-240-24XLR, NPB-360- 12TB, NPB-360-12AD1-A, NPB-360-12XLR-A, NPB-360- 24TB, NPB-360-24AD1-A, NPB-360-24XLR-A	ES1	PS3	N	Y
NPB-120-48TB, NPB-120-48AD1, NPB-120-48XLR, NPB- 240-48TB, NPB-240-48AD1, NPB-240-48XLR, NPB-360- 48TB, NPB-360-48AD1, NPB-360-48XLR	ES2	PS3	N	N
NPB-120	ES1	PS3	N	Y
NPB-360	ES1	PS3	N	Y
NSD05	ES1	PS1	N	Y
NTS-1200	ES3	PS3	N	N
NTU-1200	ES3	PS3	N	N
NTS-1700	ES3	PS3	N	N
NTU-1700	ES3	PS3	N	N
NTS-2200	ES3	PS3	N	N
NTS-3200	ES3	PS3	N	N
NTU-2200	ES3	PS3	N	N
NTU-3200	ES3	PS3	N	N
NTS-250P	ES3	PS3	N	N
NTS-400P	ES3	PS3	N	N
NTS-300	ES3	PS3	N	N
NTS-450	ES3	PS3	N	N
NTS-750	ES3	PS3	N	N
NTS-2200-248TB	ES3	PS3	N	N
OWA-200U	ES1	PS3	N	Y
P-600	ES1	PS3	N	Y
SE-600	ES1	PS3	N	Y
PB-600-48	ES1	PS3	N	Y

Model	ES Class (output circuit)	PS Class (output circuit)	Meet LPS	SELV
PB-1000	ES1	PS3	N	Y
PD-45	ES1	PS2	N	Y
PD-65	ES1	PS2	N	Y
PS-45	ES1	PS2	N	Y
PS-65	ES1	PS2	N	Y
PT-45	ES1	PS2	N	Y
PT-65	ES1	PS2	N	Y
PD-25	ES1	PS2	N	Y
PHP-3500-24, PHP-3500-48	ES1	PS3	N	Y
PHP-3500-115, PHP-3500-230, PHP-3500-380	ES3	PS3	N	N
PID-250	ES1	PS3	N	Y
PPS-125	ES1	PS3	N	Y
PPT-125	ES1	PS3	N	Y
PS-45	ES1	PS2	N	Y
PS-65	ES1	PS2	N	Y
PD-45	ES1	PS2	N	Y
PD-65	ES1	PS2	N	Y
PT-45	ES1	PS2	N	Y
PT-65	ES1	PS2	N	Y
PS-05	ES1	PS1	N	Y
PSC-35	ES1	PS2	Y	Y
PSC-60	ES1	PS2	N	Y
PSC-100	ES1	PS3	N	Y
PSC-160	ES1	PS3	N	Y
PSD-30	ES1	PS3	N	Y
PSD-45	ES1	PS2	N	Y
PSP-600	ES1	PS3	N	Y
PT-4503,6503	ES1	PS2	N	Y
QP-150	ES1	PS3	N	Y
QP-200	ES1	PS3	N	Y
QP-320	ES1	PS3	N	Y
RCP-1600	ES1	PS3	N	Y
RCB-1600	ES1	PS3	N	Y
RSP-1600	ES1	PS3	N	Y
RPB-1600	ES1	PS3	N	Y
NSP-1600	ES1	PS3	N	Y
RCB-1600NE	ES1	PS3	N	Y
RHP-1U,RHP-8K1U,RHB-8K1U	ES1	PS3	N	Y
RCP-2000	ES1	PS3	N	Y
RSP-2000	ES1	PS3	N	Y
RKP-6K1U	ES1	PS3	N	Y
RCP-1000,1U,3K1U	ES1	PS3	N	Y
RSP-1000	ES1	PS3	N	Y
RD-50	ES1	PS3	N	Y
RID-50	ES1	PS3	N	Y
RQ-50	ES1	PS3	N	Y
RS-50	ES1	PS3	N	Y
RT-50	ES1	PS3	N	Y
RD-85	ES1	PS3	N	Y
RID-85	ES1	PS3	N	Y
RQ-85	ES1	PS3	N	Y
RT-85	ES1	PS3	N	Y
RS-100	ES1	PS3	N	Y
RD-125	ES1	PS3	N	Y
RID-125	ES1	PS3	N	Y
RQ-125	ES1	PS3	N	Y
RT-125	ES1	PS3	N	Y

Model	ES Class (output circuit)	PS Class (output circuit)	Meet LPS	SELV
RS-150	ES1	PS3	N	Y
RD-35	ES1	PS2	N	Y
RS-35	ES1	PS2	N	Y
RD-65	ES1	PS2	N	Y
RT-65	ES1	PS2	N	Y
RID-65	ES1	PS2	N	Y
RQ-65	ES1	PS2	N	Y
RS-75	ES1	PS2	N	Y
RPS-60	ES1	PS2	N	Y
RPD-60	ES1	PS2	N	Y
RPT-60	ES1	PS2	N	Y
RS-50	ES1	PS2	N	Y
RD-50	ES1	PS2	N	Y
RT-50	ES1	PS2	N	Y
RID-50	ES1	PS2	N	Y
RQ-50	ES1	PS2	N	Y
RS-35	ES1	PS2	N	Y
RD-35	ES1	PS2	N	Y
RS-15	ES1	PS2	Y	Y
RS-25	ES1	PS2	N	Y
RS-100	ES1	PS3	N	Y
RD-85	ES1	PS3	N	Y
RID-85	ES1	PS3	N	Y
RT-85	ES1	PS3	N	Y
RQ-85	ES1	PS3	N	Y
RSD-30	ES1	PS2	Y	Y
RSD-60	ES1	PS2	Y	Y
RSD-100	ES1	PS3	N	Y
RSD-150	ES1	PS3	N	Y
RSD-200	ES1	PS3	N	Y
RSD-300	ES1	PS3	N	Y
RSD-500	ES1	PS3	N	Y
RSP-75	ES1	PS2	N	Y
RSP-100	ES1	PS3	N	Y
RSP-150	ES1	PS3	N	Y
RSP-200	ES1	PS3	N	Y
RSP-320	ES1	PS3	N	Y
RSP-500	ES1	PS3	N	Y
RSP-750	ES1	PS3	N	Y
RSP-1500	ES1	PS3	N	Y
RSP-2400	ES1	PS3	N	Y
RSP-3000	ES1	PS3	N	Y
RST-5000	ES1	PS3	N	Y
RST-10000	ES1	PS3	N	Y
SBP-001	ES1	PS1	Y	Y
SCP-35	ES1	PS2	N	Y
SCP-50	ES1	PS2	N	Y
SCP-75	ES1	PS2	N	Y
SD-100D	ES1	PS3	N	Y
SD-150D	ES1	PS3	N	Y
SD-200D	ES1	PS3	N	Y
SD-350D	ES1	PS3	N	Y
SD-500	ES1	PS3	N	Y
SD-1000-48	ES2	PS3	N	N
SD-1000	ES1	PS3	N	Y
SDP-001	ES1	PS1	N	Y
SDR-75	ES1	PS3	N	Y

Model	ES Class (output circuit)	PS Class (output circuit)	Meet LPS	SELV
SDR-120	ES1	PS3	N	Y
SDR-240	ES1	PS3	N	Y
SDR-480	ES1	PS3	N	Y
SDR-480P	ES1	PS3	N	Y
SDR-960	ES1	PS3	N	Y
SE-450	ES1	PS3	N	Y
SE-1000	ES1	PS3	N	Y
SE-1500	ES1	PS3	N	Y
SPV-150	ES1	PS3	N	Y
SPV-300	ES1	PS3	N	Y
TDR-480	ES1	PS3	N	Y
TDR-960	ES1	PS3	N	Y
TN-1500	ES3	PS3	N	N
TS-1500	ES3	PS3	N	N
TN-3000	ES3	PS3	N	N
TS-3000	ES3	PS3	N	N
TS-200	ES3	PS3	N	N
TS-400	ES3	PS3	N	N
TS-700	ES3	PS3	N	N
TS-1000	ES3	PS3	N	N
UHP-200(R)	ES1	PS3	N	Y
UHP-200A	ES1	PS3	N	Y
UHP-350(R)	ES1	PS3	N	Y
UHP-500(R)	ES1	PS3	N	Y
UHP-750	ES1	PS3	N	Y
UHP-1000	ES1	PS3	N	Y
UHP-1500	ES1	PS3	N	Y
UHP-1500H	ES3	PS3	N	N
UHP-2500	ES1	PS3	N	Y
UMP-400	ES1	PS3	N	Y
WDR-120	ES1	PS3	N	Y
WDR-240	ES1	PS3	N	Y
WDR-480	ES1	PS3	N	Y

[Excel documentation link](#)