The difference of draft for CISPR 32 Edition 3



The third edition of CISPR 32 is under drafted, according to the content of published DRAFT (COMMITTEE DRAFT, CD), there are three points worth paying attention to as follow:

1.Add the concept and limit requirment for the Wireless Power transmission (Wireless Power Transfer (WPT)) (such as Wireless charging equipment). Limit requirments include radiated emissions (9 k \sim 30 MHZ) and conduction emissions (9 k \sim 150 KHZ), and the type of equipment is divided into Class A and Class B. The following is limit requirment for Class B equipment.

Table A.15 – Requirements for radiated emissions at frequencies below 30 MHz of Class B

Table Frequency range .	Measurement				Class B limits	
	Facility	Antenna	Distance	Detector type / bandwidth	dB(μA/m)	dB(μA)
0,009 to 0,10	OATS/ SAC	"0,6 m" loop	3 m	Quasi Peak / 200 Hz	30	-
0,1 to 0,150					7 to 4	-
0,150 to 4,0				Quasi Peak / 9 kHz	4 to -22	-
4,0 to 30					-22	-
0,009 to 0,10				Quasi Peak /	-	50
0,10 to 0,150	Anv	11.45		200 Hz	-	27 to 24
0,150 to 4,0	Ally	LLAS	-	Quasi Peak /		24 to -2.5
4,0 to 30				9 kHz	-	-2.5 to -7
	MHz 0,009 to 0,10 0,1 to 0,150 0,150 to 4,0 4,0 to 30 0,009 to 0,10 0,10 to 0,150 0,150 to 4,0	MHz Facility 0,009 to 0,10 0,1 to 0,150 0,150 to 4,0 4,0 to 30 0,009 to 0,10 0,10 to 0,150 0,150 to 4,0 Any	Frequency range MHz Facility Antenna 0,009 to 0,10 0,1 to 0,150 0,150 to 4,0 4,0 to 30 0,009 to 0,10 0,10 to 0,150 0,150 to 4,0 Any LLAS	Frequency range MHz Facility Antenna Distance 0,009 to 0,10 0,1 to 0,150 0,150 to 4,0 4,0 to 30 0,009 to 0,10 0,10 to 0,150 0,150 to 4,0 Any LLAS -	Frequency range MHz Facility Antenna Distance Detector type / bandwidth 0,009 to 0,10 0,1 to 0,150 OATS / SAC OATS / SAC O,150 to 4,0 0,009 to 0,10 0,10 to 0,150 Any LLAS Quasi Peak / 200 Hz Quasi Peak / 200 Hz Quasi Peak / 200 Hz Quasi Peak / 200 Hz	Frequency range MHz Facility Antenna Distance Detector type / bandwidth dB(μA/m)

Table A.17 – Requirements for conducted emissions at frequencies below 150 kHz from the AC mains power ports of Class B equipment with WPT ports

	Fraguenav ranga	Mea	surement	Class B limits
Table Fre	Frequency range MHz	Coupling device (see Table A.8)	Detector type / bandwidth	dB(μV)
A17.1	0,009 to 0,050	AMNI	Quasi Peak / 200 Hz	110
	0,050 to 0,150	AMN	Quasi Feak / 200 HZ	90 to 80
These limits	only apply when the WPT f	unction is active.		

Apply the requirements of A.15.1 or A.15.2 across the entire frequency range

These limits only apply when the WPT function is active

The difference of draft for CISPR 32 Edition 3



- 2. Modify the limit requirment of radiated emissions above 1 GHz
- To adjust the limit requirment of 1 GHz \sim 3 GHz are the same as limit requirments of 3 GHz 6 GHz. The following is the limit requirments for Class B equipment :
- NOTE: The second edition of the Class B equipment limit requirment :

Average: 50 dB (1-3 GHz), 54 dB (3-6 GHz) Peak: 70 db (1-3 GHz), 74 db (3-6 GHz)

Table A.5 – Requirements for radiated emissions at frequencies above 1 GHz for class B equipment

Table Frequency range MHz	Frequency range	Measurement			Class B limits	
	Facility (see table A.1)	Distance m	Detector type/ bandwidth	dB(μV/m		
A5.1	1 000 to 6 000	FSOATS	3	Average/ 1 MHz	54	
A5.2	1 000 to 6 000			Peak/ 1 MHz	74	
A5.3	1 000 to 6 000	DV6	n/a	Average / 1 MHz	54	
A5.4	1 000 to 6 000	RVC		Peak / 1 MHz	74	

Apply A5.1 and A5.2 or A5.3 and A5.4 across the frequency range from 1 000 MHz to the highest required frequency of measurement derived from Table 1.

These requirements are not applicable to the local oscillator and harmonics frequencies of equipment covered by Table A.7.

The difference of draft for CISPR 32 Edition 3



- 3, Add concept and limit requirment of the DC power port (DC distribution network. The DC power port).
- The following is the limit requirment for DC power port of Class B equipment, these limit requirments are the same as limit requirments for AC power port of Class A equipment.

Table A.YY – Requirements for conducted emissions from the DC power ports of Class B equipment

Applicable to 1. DC power ports (3.1.12) where the connection from the DC port to the power source may be with a cable 3m or greater in length						
Table Frequency range clause MHz		Coupling device (see Table A.8)	Detector type / bandwidth	Class B limits dB(μV)		
AY.1	0,15 to 0,5	AMM	. Quasi Peak / 9 kHz	79		
	0,5 to 30	AMN		73		
AY.2	0,15 to 0,5	AMM	Average / 9 kHz	66		
	0,5 to 30	AMN		60		





• 4. The International Electrotechnical Commission expects this regulation to be released on 2026-12-11.

